



Parameter	Value	Type	Unit	Min	Max
Enable SattBus on TCP/IP	false	bool			
Routing method	mip	enum			
Default gateway		string			150
AE System AE class	99E0	dint		1	9999
AE System AE low severity	200	dint		1	1000
AE System AE medium severity	400	dint		1	1000
AE System AE high severity	600	dint		1	1000
AE System AE critical severity	800	dint		1	1000
AE System AE fatal severity	1000	dint		1	1000
AE System events to controller log	Medium Severity	enum			
AE Local printer event queue size	300	dint		10	3000
AE Max no of local printer event queues	0	dint		0	5
AE Event subscription queue size	300	dint		200	3000
AE Max number of event subscriptions	3	dint		0	7
AE Event subscription time out	360	dint	min	0	1440
AE Buffer size of low level event	2	dint		2	4000
AE Max no of Named Value items	0	dint		0	9000
AE Limit auto disable	3	dint		0	127
RNRP Default network ID	172.16.0.0	string			150
RNRP Number of own areas	2	dint		1	4
RNRP Number of remote areas	4	dint		0	15
RNRP Max Lost Messages	3	dint		1	10
RNRP Send Period	1	dint	s	1	60
RNRP Max no of hops	3	dint		1	5
RNRP Ext network		string			150
RNRP Ext netw mask		string			150
RNRP Ext router1 addr		string			150
RNRP Ext router2 addr		string			150
Tool Routing	Disabled	enum			
Tool Routing max: no of connections	20	dint		5	50
CS CNCP ClockMaster Order No	1	dint		0	10
CS Protocol Type	No Synch	enum			
CS Time Set Enabled	True	enum			
CS Synch Interval	10	dint	s	1	240
CS SNTP ServerAddr: 1		string			150
CS SNTP ServerAddr: 2		string			150

Name	Value	Description
HWState	16#00000002	Warning
HWStateChangeTime	2018-06-01-14:30:29.874	Time when error or warning occurred
ErrorsAndWarnings	16#30E0000	Warning on primary unit, Warning on backup unit,
ExtendedStatus	16#C0000000	Redundant mode enabled, Unit B acts primary
LatchedErrorsAndWarnings	16#67E0000	Warning on primary unit, Warning on backup unit,
LatchedExtendedStatus	16#00000003	Backup CPU stopped, Switchover occurred, Redundant

Hardware - Controller_1.0.1 Ethernet

Parameter	Value	Type	Unit	Min	Max
IP address	172.16.0.1	string			150
IP subnet mask	255.255.252.0	string			150
Network Area	3	dint		0	35
Path Number	0	dint		0	1
Node Number	0	dint		0	500
Network Area Local	false	bool			
Send Period	1	dint	s	1	60
Max Lost Messages	3	dint		1	10
Proxy router	0.0.0.0	string			150
Target address	0.0.0.0	string			150

Settings Connections Unit Status

Hardware - Controller_1.0.1 Ethernet

Name	Value	Description
HWState	16#00000002	Warning
HWStateChangeTime	2018-06-01-14:30:29.875	Time when error or warning occurred
ErrorsAndWarnings	16#00000000	
ExtendedStatus	16#00000000	
LatchedErrorsAndWarnings	16#60020000	No communication BackupCPU, No communication
LatchedExtendedStatus	16#00000000	

Settings Connections Unit Status

Hardware - Controller_1.0.2 Ethernet

Parameter	Value	Type	Unit	Min	Max
IP address	172.16.0.0	string			150
IP subnet mask	255.255.252.0	string			150
Network Area	0	dint		0	35
Path Number	0	dint		0	1
Node Number	0	dint		0	500
Network Area Local	false	bool			
Send Period	1	dint	s	1	60
Max Lost Messages	3	dint		1	10
Proxy router	0.0.0.0	string			150
Target address	0.0.0.0	string			150
Enables Ethernet channel	false	bool			
Mode Ethernet channel	Autonegotiate	enum			

Settings Connections Unit Status

Hardware - Controller_1.0.2 Ethernet

Name	Value	Description
HWState	16#00000000	Status OK
HWStateChangeTime	2018-06-01-14:29:12.050	System startup time
ErrorsAndWarnings	16#00000000	
ExtendedStatus	16#00000000	
LatchedErrorsAndWarnings	16#00000000	
LatchedExtendedStatus	16#00000000	

Settings Connections Unit Status